Owl 640 II

Low noise, digital VIS-SWIR camera 640 x 512 \cdot 15µm x 15µm Pixel Pitch \cdot Frame rate up to 120 Hz \cdot





Key Features and Benefits

The best performing VIS-SWIR camera in the World!

- VIS-SWIR technology Compatible with VIS-SWIR illuminators, markers & pointers
- 15µm x 15µm pixel pitch Enables highest resolution VIS-SWIR image
- Ultra high intrascene dynamic range Enables similtaneous capture of bright & dark portions of a scene
- On-board Automated Gain Control (AGC) Enables clear video in all light conditions
- Ultra compact, Low power Ideal for hand-held, mobile or airborne systems

Resolution	640 x 512
Frame rate	Up to 120Hz
Readout noise	36 electrons
Wavelength Range	VIS-SWIR




www.raptorphotonics.com

Specification for Owl 640 II

Sensor Type	InGaAs PIN-Photodiode	
Active Pixel	640 x 512	
Pixel Pitch	15μm x 15μm	
Active Area	9.6mm x 7.68mm	
Spectral response ¹	0.4µm to 1.7µm	
Readout Noise (RMS)² LG = Low Gain HG = High Gain	LG: <190e- (174e- typical) HG: <50e- (36e- typical)	
Peak Quantum Efficiency	>90% @1.3µm	
Full Well Capacity	LG: 650ke- HG: 10ke-	
Pixel Operability	>99.5%	
Dark Current (e/p/s)	<28,000 @ 15°C	
Digital Output Format	14 bit Camera Link (Base Configuration)	
Exposure time ³	10µs to 26.8s	
Shutter mode	Global shutter	
Frame Rate	Up to 120Hz	
Optical Interface	C mount or M42	
Dynamic Range	LG: 71dB HG: 49dB	
Trigger interface	Trigger IN and OUT - TTL compatible	
Power supply	12V DC ±0.5V	
TE Cooling	Active	
Image Correction	3 point NUC (offset, Gain & Dark Current) + pixel correction	
Functions controlled by serial communication	Exposure, intelligent AGC, Non Uniformity Correction, Gamma, Pk/Av, TEC, ALC ROI	
Camera Power Consumption ⁴	<4W with TEC ON, NUC ON	
Operating Case Temperature ⁵	-20°C to +55°C	
Storage Temperature	-30°C to +60°C	
Dimensions (L*W*H)6	69.4mm x 50.00mm x 50.00mm	
Weight	282g	
Raptor Photonics Limited reserves the right to change this document at any time without notice and		

Raptor Photonics Limited reserves the right to change this document at any time without notice and disclaims liability for editorial, pictorial or typographical errors.

Quantum Efficiency



^{*}Data supplied by sensor manufacturer



Willowbank Business Park Larne, Co Antrim BT40 2SF, Northern Ireland Raptor Photonics Ltd. (UK) T: +44(0)2828 270 141 E: sales@raptorphotonics.com www.raptorphotonics.com

Ordering Information

Camera

Owl 640 II Digital Camera	OW1.7-VS-CL-640-II
Power Supply Cable	RPL-HR4-K
Optional Accessories	
Mini PC with XCAP Std and frame grabber	RPL-PC-EL1
EPIX® EB1 Frame Grabber	RPL-EPIX-EB1
EPIX® XCAP Std software	RPL-XCAP-STD
Camera Link Cable (2m) ⁷	RPL-MCL-CBL-2M
Optical Lenses ⁸	RPL-xx-xxxx

Note 1: Optional filters available: Low, High or bandpass.
Note 2: Typical readout noise is calculated from an average of the last 20 cameras shipped.
Note 3: In practice, the maximum exposure time will be dark current limited.
Note 4: Measured in an ambient of 25°C with adequate heat sinking. For more detailed power consumption values, please refer to the user manual.
Note 5: Extended operating temperature range on request.
Note 6: Dimensions include all connector parts on the camera interface.
Note 7: Longer Camera Link cable available.

Note 7: Longer Camera Link cable available. Note 8: Please consult us to check our range of lenses.

Demo is available on request. Pricing AOR subject to volumes.

Detailed technical drawings can be downloaded at www.raptorphotonics.com

Applications

Surveillance

- 860, 1064 & 1550nm laser line detection
- Active Imaging
- Airborne Payload
- Hand Held Systems
- Imaging through Fog
- Range Finding
- Vision enhancement

Scientific

- Astronomy
- Beam Profiling
- Hyperspectral Imaging
- Semiconductor Inspection
- Solar Cell Inspection
- Thermography

Raptor Photonics Inc. (USA) T: +1 (877) 230-4836 E: sales@raptorphotonics.com www.raptorphotonics.com



