

Compatibility Table

	PPMS® DynaCool®	PPMS® VersaLab®	PPMS® (legacy product)
AC Resistance (ETO)	D605	V605	P605 [Req. Model 1000]
DC Resistance	D400A [Incl. D415]	V400 [Incl. V415]	P400A
Rotator	D310A/B [Incl. D415]	V310A/B [Incl. V415]	P310A/B
VSM	D525	V525	P525 [Incl. Model 1000, Req. P945]
VSM Large Bore	D529 [Req. D525]	V529 [Req. V525]	P529 [Req. P525]
VSM Oven	D527 [Req. D525]	V527 [Req. V525]	P527 [Req. P525, P640]
FORC Software	D181 [Req. D525]	V181 [Req. V525]	P181 [Req. P525]
FOSH	D320 UV/IR [Req. D525]	n/a	P320 UV/IR [Req. P525]
Pressure Cell (Magnetometry)	D421 [Req. D525]	V421 [Req. V525]	P421 [Req. P525]
Torque Magnetometer	D550 [Req. D310]	V550 [Req. V310]	P550 [Req. P400A, P310]
ACMS II	D505A [Req. D525]	V505A [Req. V525]	P505A [Req. P525]
Thermal Transport	D670	V670	P670 [Req. Model 1000, P640]
Heat Capacity	D650	V650	P650C [Req. Model 1000, P640]
Dilatometer	D680	n/a	P680 [Req. Model 1000]
CryoFMR	D882A/D880A/D885A/D887A [Req. D415]	V882A/V880A/V885A	P882A/P880A/P885A/P887A
Cryo ST-FMR	D888A/D889A [Req. D415]	V888A/V889A	P888A/P889A
Adiabatic Demagnetization Refrigerator	D810 [Req. D605 or D400A]	n/a	P810 [Req. P640, P605 or P400A]
Helium-3 Refrigerator	D825A/AV	n/a	P825C/CV [Req. Model 1000, P640]
Dilution Refrigerator	D850A	n/a	P850A [Req. Model 1000, P640]
MFP Types A/G/M	D450A/G/M [Req. D415]	V450A/G/M [Req. V415]	P450A/G/M
MFP Types B/C	D450B/C	V450B/C	P450B/C
MFP Photoconductivity	D790A/B [Req. D415, Light Source]	n/a	P790A/B [Req. Light Source]
MFP CryoFMR	D886B [Req. D415]	V886B	P886B
Optical MFP	D725A/B [Req. D415]	V725A/B [Req. V415]	P725A/B

Sub-Kelvin Compatibility Kits

	Range	ETO (D605) / (P605)	Resistivity (D400A) / (P400A)	Heat Capacity (D650) / (P650C)	AC Suscept. for DR (D860) / (P860)
ADR	300 K – 0.1 K	Compatible	Compatible	n/a	n/a
³ He	350 K – 0.4 K	Compatible	Compatible	+ D826A/AV / P826A/AV	n/a
DR	4 K – 0.05 K	+ D605-DR / P605-DR	Compatible	+ D856A / P856A	Compatible